

---

## Dolphon® XL-2102 1K Resin

Dolphon® XL-2102 is a transparent, low emission, 1K resin based on polyester.

---

### Attributes

Dolphon® XL -2102 is characterised by the following properties:

- Excellent wetting properties
- Approved for railway applications acc. EN 45545-2: HL3 for R22 and R23
- Low weight loss on cure
- Very low odour
- Relatively fast cure cycles

---

### Application

Dolphon® XL-2102 is a proven resin for impregnating stators, rotors, transformers, traction coils and inductances.

---

### Standards

- UL-approved Class H (180 °C), File OBOR2.E317427 and OBJS2.E317429
- UL-System-approved 130 - 220 °C
- EN 45545-2: HL3 for R22 and R23

UL-approved with magnet wire temperature class according to UL 1446:

#### Magnet wire Twisted pairs Helical coils

MW 16-C	220 °C	-
MW 28-C	130 °C	-
MW 35-C	180 °C	200 °C

---

### Delivery forms

Dolphon® XL-2102 is delivered in 25 kg disposable containers, 230 kg barrels and 1000 kg containers.

---

### Storage

Dolphon® XL -2102 can be stored for 18 months at room temperature in a sealed container (max. 30 °C). The dip resin must be stored in a suitable place and protected against direct sunlight, UV radiation and sources of heat.

Always observe general rules and regulations.

---

### Hardening

The curing time commences once the object temperature has been reached.

---

Typical curing time:

at 150 °C - 1 h\*

at 130 °C - 3-4 h\*

at 120 °C - 5-7 h\*

\*(Full curing is measured by DSC. The time must be taken after units reach the baking temperature). For objects having to endure high mechanical or chemical stress during service, longer curing times are recommended.

Best results will be achieved at:

150 °C - 2.5 h

160 °C - 2 h

170 °C - 75 min.

---

## Protection

Cured Dolphon® XL-2102 is biologically inactive and safe to health. Always refer to the safety data sheet and implement protective measures when processing the liquid dip resin.

---

## Processing

Exemplary impregnating process suggestion:

1. Preheat the units at 50-60 °C (max.)
2. Dip into the resin for 30-60 min.
3. Drain for 1 h min.
4. Bake 1 h at 150 °C\* (see "Curing")

For the VPI application the cycle must be set for each type of machines. Feel free to contact us.

---

## Cleaning

Since the cured dip resin is practically insoluble, the tools have to be cleaned as soon as possible with a suitable solvent. Maintenance and care of impregnating plants, especially cleaning, must be carried out according to operational requirements. Always refer to the user manual of the plant.

Mechanical	Unit of measure	Conditions	Value	Test method
Gel time	min	100 °C	30-45	
Weight loss	%	10 g cured 1 h at 150°C	< 3.5	
Bond strength	N	at 25 °C	>180	IEC 61033, HC, 1h/150 °C
Bond strength	N	at 80 °C	>90	IEC 61033, HC, 1h/150 °C
Bond strength	N	at 155 °C	>30	IEC 61033, HC, 1h/150 °C

Thermal	Unit of measure	Conditions	Values	Test method
Thermal conductivity	W/mK		0.25-0.30	

Electrical	Unit of measure	Conditions	Value	Test method
Dielectric strength	kV/mm	0.025 mm film	>128	ASTM D-115
Volume resistivity	$\Omega \times \text{cm}$		$>10^{15}$	IEC 60464-2
Volume resistivity	$\Omega \times \text{m}$	after 7 d water storage	$>10^{12}$	IEC 60464-2
Surface resistivity	$\Omega$		$>10^{15}$	IEC 60464-2

The information on this data sheet is based on the information provided by our supplier. It does not represent any specification or agreements regarding conditions or properties. The indicated values are standard values. Deviations from those values due to production and application cannot be excluded. The information on this data sheet is addressed to experts who use it at their own discretion and at their own risk. We do not guarantee results, or accept liability for the indicated specifications or for results obtained based on the specifications. Please contact us for more detailed information. Non-toxic and toxic substances are listed on the safety data sheet.

Updated 04/24

Dolphon®, SYNTHITE® are registered trademarks of John C. Dolph Company (Dolphs).



Electrical	Unit of measure	Conditions	Value	Test method
Dielectric constant		at 25 °C	3.3	ASTM D-150
Creep resistance		CTI	>600	IEC 60112

Chemical	Unit of measure	Conditions	Value	Test method
Water absorption	%	90 min at 100 °C	<1.5	ASTM D 570
Water absorption	%	24h at 25 °C	<1	ASTM D 570
Resistance		Xylene, Methanol, Hexane	yes	IEC 60464-2
Resistance		10% hydrochloric acid	< 2.5 %	ISO 175 - 7 d storage
Resistance		30% sulfuric acid	< 1.5 %	ISO 175 - 7 d storage
Resistance		transformer oil	< 0.5 %	ISO 175 - 7 d storage
Resistance		unleaded gasoline	< 1.5 %	ISO 175 - 7 d storage
Resistance		cleaning agents	< 1.5 %	ISO 175 - 7 d storage

Liquid phase	Unit of measure	Conditions	Values	Test method
--------------	-----------------	------------	--------	-------------

The information on this data sheet is based on the information provided by our supplier. It does not represent any specification or agreements regarding conditions or properties. The indicated values are standard values. Deviations from those values due to production and application cannot be excluded. The information on this data sheet is addressed to experts who use it at their own discretion and at their own risk. We do not guarantee results, or accept liability for the indicated specifications or for results obtained based on the specifications. Please contact us for more detailed information. Non-toxic and toxic substances are listed on the safety data sheet.

Updated 04/24

Dolphon®, SYNTHITE® are registered trademarks of John C. Dolph Company (Dolphs).



Liquid phase	Unit of measure	Conditions	Values	Test method
Viscosity	s	at 25 °C	110-170	Ford Cup 4
Specific density	g/cm <sup>3</sup>	at 25 °C	1.12 ± 0.03	

The information on this data sheet is based on the information provided by our supplier. It does not represent any specification or agreements regarding conditions or properties. The indicated values are standard values. Deviations from those values due to production and application cannot be excluded. The information on this data sheet is addressed to experts who use it at their own discretion and at their own risk. We do not guarantee results, or accept liability for the indicated specifications or for results obtained based on the specifications. Please contact us for more detailed information. Non-toxic and toxic substances are listed on the safety data sheet.

Updated 04/24

Dolphon®, SYNTHITE® are registered trademarks of John C. Dolph Company (Dolphins).

